





Q7defend

Light control function



Changing Battery




Additional online information



FOR MORE INFO



Hyperfocus and Focuslock



Specifications



Warning and Changing Colorfilter



Steiner A/S
P.O. Pedersens Vej 14A
DK-8200 Aarhus N
Phone: +45 87 52 52 12
Fax: +45 87 52 52 15
Contact: info@suprabeam.com
www.suprabeam.com

Miniature in size but surprisingly powerful. It is equipped with our Hyper-Focus system and combined with the latest LED Power-Chip technology.

MINI PEN TORCH WITH FOCUS

PERFECT FOR KEYRING

LIGHTWEIGHT AT ONLY 38 GRAMS

LIGHT AT YOUR FINGERTIPS...
Q1mini



EN

OPERATING

The Q7defend has 5 light functions and 4 main light intensities: Max, Strobe, High, Medium and Low.

Press the switch completely down to turn on the Q7defend in Max mode.

The different light functions are activated by pressing the switch repeatedly within 2 sec. Pressing and releasing the switch halfway makes it possible to toggle swiftly between light modes.

In any light mode, simply press the switch once to turn it off.

HYPERFOCUS™

The light beam angle of the Q7defend is adjustable from 10° to 70° by sliding the torch head back and forth. The torch head can be locked in the selected position by rotating left.

CHANGING COLORFILTER

To change the colorfilter, remove the strike bezel. Remove the metal ring and replace it with the colorfilter of your selection. The colorfilters are sold separately and comes in red, green, blue and yellow.

BATTERIES

Pay attention to the polarity of the batteries when placing them in the Q7defend. To protect the environment, this product is compatible with rechargeable batteries 1.2-1.5V (not Li-ion 3.7V). We highly recommend using Premium type batteries only to ensure high quality light output and long lighting time. We can not guarantee the light data if using battery types of lower quality.

MAINTENANCE

Please make sure that the

Q7defend is clean, especially around the movable or sliding parts. You can clean it with a damp cloth. Pay special attention to the union of the tail cap. Dirt on this area could impair the correct contact of the batteries. Repairs may only be carried out by authorized personnel.

WARRANTY

We provide 5 years limited warranty. This warranty does not include normal maintenance and services and does not apply to batteries nor any products or parts which have been subject to modification, misuse, negligence, accident, improper repair by anyone other than SUPRABEAM.

DISPOSAL

Dispose this product in an environmentally compatible manner in accordance with national regulations, if in doubt about correct disposal please contact your municipal authority that can provide information about correct disposal.

EYE SAFETY

Do not look directly into the beam. The intense light can damage your eyes. The torch is classified in LED Risk Group 2 (IEC 62471)

For further information and instructions, please go to suprabeam.com

DE

BETRIEB

Die Q7defend verfügt über 5 Lichtfunktionen und 4 Lichtintensitäten: Max, Strobe, Hoch, Medium und Niedrig.

Drücken Sie den Schalter ganz nach unten, um die Q7defend in den Modus Max zu schalten.

Die verschiedenen Lichtfunktionen werden durch mehrmaliges Drücken des Schalters innerhalb von 2 s aktiviert. Drücken Sie den Schalter halb und lassen Sie ihn schnell wieder los, um zwischen den Lichtmodi umzuschalten.

Drücken Sie zum Ausschalten in jedem Lichtmodus einfach einmal auf den Schalter.

HYPERFOCUS™

Der Lichtstrahlwinkel der Q7defend ist durch Schieben des Lampenkopfes vor und zurück von 10° bis 70° einstellbar. Durch Drehen nach links kann der Lampenkopf in der gewählten Position verriegelt werden.

WECHSEL DES FARBFILTERS

Für den Wechsel des Farbfilter entfernen Sie die Schutzblende. Entfernen Sie den Metallring und ersetzen Sie ihn mit dem Farbfilter Ihrer Wahl. Die Farbfilter sind gesondert erhältlich (in den Farben rot, grün, blau und gelb).

BATTERIEN

Achten Sie beim Einlegen der Batterien in die Q7defend auf korrekte Polarität. Zum Schutz der Umwelt ist dieses Produkt mit wiederaufladbaren Batterien 1.2-1.5 V kompatibel (nicht Lithium-Ionen 3.7 V). Wir empfehlen dringend, ausschließlich hochwertige Batterietypen zu verwenden, um eine hohe Lichtausbeute und eine lange Beleuchtungszeit zu gewährleisten. Bei Einsatz minderwertiger Batterietypen können wir die Lichtdaten nicht garantieren.

WARTUNGSHINWEISE

Bitte achten Sie darauf, dass die Q7defend sauber ist (vor allem die beweglichen Teile und deren Umge



